

# Omnicare Ultra+ Align

Thermostatic Electric Shower

## Product Codes

Omnicare Ultra+ Align 8.7kW with Extended Kit	CINCULTP08W
Omnicare Ultra+ Align 9.8kW with Extended Kit	CINCULTP09W
Omnicare Ultra+ Align 8.7kW with Grab Kit	CINCULTP08WGRB
Omnicare Ultra+ Align 9.8kW with Grab Kit	CINCULTP09WGRB

## Installation

- Multiple pipe and cable entry points, a generous footprint, the Omnicare Ultra+ Align is designed with ease of replacement in mind
- Omnicare Ultra+ Align connects to analogue pumps

## Commissioning

- Simple 2 minute commissioning process

## End User

- Large soft press start/stop button
- Power on illumination along with audible feedback allows ease of use for all users
- Tactile temperature dial with soft grey tones offers helpful visual contrast
- Looped lever handle with low resistance operation
- SafeSet™ limits the maximum water temperature to 43°C, in line with guidance from our consultants in the OT Service. The unit can alternatively be configured to 41°C, meeting the BEAB Care Standard or a higher maximum temperature
- Tri-Care™ technology keeps the water temperature within +/- 1°C complying with BEAB Care approval
- Set the duration of the shower ranging from 5 minutes to 30 minutes
- Omnicare Ultra+ Align with Extended Kit - assists showering whether standing or seated, featuring an extended riser rail with a 2m anti-twist hose, or an optional dual-purpose Grab Riser Rail Kit - designed to withstand up to 150kg support load, also with a 2m anti-twist hose
- Easy clean 5 spray pattern shower head, with removable faceplate
- Single hand operated handset holder with easy push system
- Enabling the Omnicare Ultra+ to be switched on and off from outside the unit (ideal for carers), a wired remote start/stop button is available separately as an accessory



Omnicare Ultra+ Align with Extended Kit



Omnicare Ultra+ Align with Grab Kit



**SAFETY CRITICAL  
TRITON ACCESSORY**

# Omnicare Ultra+ Align

Thermostatic Electric Shower

## Shower

Temperature stability	Thermostatic +/-1°C with Tri-Care™ (1)
Power ratings	8.7kW & 9.8kW (at 240V)
Finish	White
Adjustable max temperature	41°C, 43°C or Max
Timed auto shutdown	5, 10, 20 or 30 mins (default 20 mins)
Start/stop type	Electronic soft press button
Controls	Start/stop button & temperature control dial
Audible feedback	Start/stop and timer end confirmation
Visual indicators	Power-on/timer/low flow illumination
Water connection	½" BSP male thread for 15mm compression fitting (swivel inlet (up/down))
Terminal block	16mm² max cable
Waste pump connection(s)	Analogue wired
Water supply	Mains cold water
Water pressure min	Minimum maintained pressure: 0.5 bar Minimum maintained pressure for BEAB Care: 1.0 bar
Water pressure max	10 bar (static)
Removable pipe/cable trims	Top & bottom
Other installation aid(s)	Wall mounting template

### Diagram Key:

 Water Entry Points


 Cable Entry Points

### Dimensions:

H: 400mm

W: 213mm

D: 117mm



## Riser Rail Kit

### Extended Kit Option

Length	1080mm
Diameter	25mm
Material	Stainless Steel
Finish	Polished
Hose	2m Anti-twist Chrome

### Grab Kit Option

Length	1100mm
Material	Stainless Steel
Finish	Polished
Support load (max)	150kg
Fixing brackets	5 fixing points / 70mm diameter
Hose	2m Anti-twist Chrome



2m Anti-twist Hose - Chrome  
TSHG1266



Omnicare Grab Kit  
(1100mm) White  
GAUPGF1



Omnicare Extended Kit  
(1080mm) White  
GAUPF1



Inclusive Showerhead  
(5 Spray Pattern)  
TSHECAREWHT



Remote Start / Stop  
CSGPRSS

## IMPORTANT MAINTENANCE NOTICE

Replacing specified Triton accessories for this Omnicare unit will aid optimum performance and keep the unit within the allocated guarantee period

Contact our specification team

Call: 02476 324 776 | Email: [specification@tritonshowers.co.uk](mailto:specification@tritonshowers.co.uk) | Web: [www.tritonshowers.co.uk/specifiers](http://www.tritonshowers.co.uk/specifiers)