

Omnicare Design with Grab Rail

Thermostatic Electric Shower

Product Codes

| | |
|-------------------------------------|-----------|
| Omnicare Design 8.5kW with Grab Kit | TEOMNDG81 |
| Omnicare Design 9.5kW with Grab Kit | TEOMNDG91 |

Installation

- Multiple pipe and cable entry points, a generous footprint and a fixing hole kit, the Omnicare Design with Grab Rail is designed with ease of replacement in mind
- Suitable for connection with an analogue waste pump

Commissioning

- Simple 2 minute commissioning process

End User

- Large soft press start/stop button
- Power on illumination along with audible feedback allows ease of use for all users
- Tactile temperature dial with soft grey tones offers helpful visual contrast
- Looped lever handle with low resistance operation
- Constantly regulating water temperature within +/- 1°C, (BEAB Care standard)
- Set the duration of the shower ranging from 5 minutes to 30 minutes
- Dual purpose Grab Riser Rail designed to withstand up to 150kg support load
- 2m hose and a lower level handset holder offered with the Grab Riser Rail, providing flexibility for seated or standing showering
- Easy clean inclusive 5 spray pattern showerhead with removable spray plate



SAFETY CRITICAL
TRITON ACCESSORY

Omnicare Design with Grab Rail

Thermostatic Electric Shower

Shower


| | |
|----------------------------|--|
| Temperature stability | Thermostatic +/-1°C with Tri-Therm™ |
| Power ratings | 8.5kW & 9.5kW (at 240V) |
| Finish | White |
| Adjustable max temperature | 41°C, 43°C or Max |
| Timed auto shutdown | 5, 10, 20 or 30 mins (default 20 mins) |
| Start/stop type | Electronic soft press button |
| | Start/stop button & temperature control dial |
| Audible feedback | Start/stop and timer end confirmation |
| Visual indicators | Power-on/timer/low flow illumination |
| Water connection | 15mm swivel inlet (up/down) |
| Terminal block | 16mm max cable |
| Waste pump connection(s) | Analogue |
| Water supply | Mains cold water |
| Water pressure min | Minimum maintained pressure: 0.5 bar Minimum maintained pressure for BEAB Care: 1.0 bar |
| Water pressure max | 10 bar (static) |
| Removable pipe/cable trims | Top & bottom (15mm pipework & 38mm cable trunking) |
| Other installation aid(s) | Wall mounting template |

Diagram Key:

- Water Entry Points
- Cable Entry Points

Dimensions:

- H: 387mm
- W: 240mm
- D: 116mm



Riser Rail Kit

| | |
|---------------------|---------------------------------|
| Grab version | |
| Length | 940mm |
| Material | Stainless Steel |
| Finish | Polished |
| Support load (max) | 150kg |
| Fixing brackets | 5 fixing points / 70mm diameter |
| Hose | 2m Anti-twist Chrome |

IMPORTANT MAINTENANCE NOTICE

Replacing specified Triton accessories for this Omnicare unit will aid optimum performance and keep the unit within the allocated guarantee period



Omnicare Design Grab Kit
GAOMDGF1



2m Anti-twist Hose - Chrome
TSHG1266



Inclusive Showerhead
(5 Spray Pattern)
TSHECAREWHT

Contact our specification team

Call: 02476 324 776 | Email: specification@tritonshowers.co.uk | Web: www.tritonshowers.co.uk/specifiers

(1) Tri-Therm™ constantly regulating flow, blending water and adjusting the power to precisely control the showering temperature.
 (2) Safe-Set™ tamper proof maximum temperature setting whilst allowing full rotation of the temperature dial.
 (3) The shower will operate down to 0.5 bar at reduced flow rates.